

## PBMN low pressure

Fully welded pressure transmitter for industrial applications

PBMN-2#####2##0##

### Overview

- Excellent accuracy and active temperature compensation for precise pressure measurements
- Measuring range from -0.1 ... 0.1 bar up to 0 ... 40 bar
- Universal field of applications due to fully welded and robust stainless steel housing
- ATEX approval
- Absolute pressure, relative pressure and vacuum measurement
- External programming of zero point and span with FlexProgrammer 9701



### Technical data

#### Performance characteristics

Pressure type	Absolute Relative (gauged)
Compensated temperature range	-40 ... 85 °C
Long term stability	≤ 0.1 % FSR/a, measuring range > 1 bar ≤ 1 mbar, measuring range ≤ 1 bar
Max. measuring error	± 0.1 % FSR ± 0.25 % FSR Including zero-point and span error, non-linearity (by terminal base line), hysteresis and non-repeatability (EN 61298-2) For turndown, multiply this value by the applied turndown ratio
Max. measuring span	40 bar
Max. turndown ratio	5 : 1
Measuring range	-1 ... 40 bar
Standard error of measurement (BFSL)	± 0.04 % FSR ± 0.1 % FSR Including non-linearity, hysteresis and non-repeatability according BFSL
Min. measuring span	0.1 bar
Rise time (10 ... 90 %)	≤ 5 ms
Temperature coefficient	≤ 0.03 % FSR/10 K, measuring span ≤ 0.03 % FSR/10 K, zero point

#### Process conditions

Process temperature	-40 ... 120 °C
Process pressure	Refer to section "Operating conditions"

#### Process connection

Connection variants	Refer to section "Dimensional drawings"
Wetted parts material	AISI 316L (1.4404)
Wetted parts material, membrane	AISI 316L (1.4435)

#### Process connection

Wetted parts material, gas-ket	FKM (Viton®) gaskets require a minimum ambient temperature of -20 °C and a minimum medium temperature of -25 °C NBR, optional
--------------------------------	--

#### Ambient conditions

Operating temperature range	-40 ... 85 °C
Storage temperature range	-40 ... 85 °C
Degree of protection (EN 60529)	IP 65, with connector DIN EN 175301-803 A (DIN 43650 A), 4-pin IP 67, with cable outlet IP 67, with connection head IP 67, with connector M12-A, 4-pin
Insulation resistance	> 100 MΩ, 500 V DC
Bump (EN 60068-2-27)	100 g / 2 ms, 4000 impulses per axis and direction
Shock (EN 60068-2-27)	50 g / 11 ms, 100 g / 6 ms, 10 impulses per axis and direction
Vibration (sinusoidal) (EN 60068-2-6)	1.5 mm p-p (10 ... 58 Hz), 10 g (58 Hz ... 2 kHz), 10 cycles (2.5 h) per axis
Vibration, broad-band random (EN 60068-2-64)	0.1 g <sup>2</sup> / Hz, > 10 gRMS (20 Hz ... 1 kHz), 30 min. per axis

#### Output signal

Current output	4 ... 20 mA, 2-wire 20 ... 4 mA, 2-wire
Voltage output	0 ... 10 V, 3-wire 0 ... 5 V, 3-wire 0.5 ... 4.5 V, 3-wire 1 ... 5 V, 3-wire 10 ... 0 V, 3-wire
Load resistance	≥ 5 kΩ
Short circuit protection	Yes
Shunt resistance	R <sub>s</sub> ≤ (V <sub>s</sub> - 8 V)/0.0205 A R <sub>s</sub> ≤ 750 Ω, V <sub>s</sub> = 24 V

# PBMN low pressure

Fully welded pressure transmitter for industrial applications

PBMN-2#####2##0##

## Technical data

### IO-Link interface

IO-Link version	1.1
IO-Link port type	Class A
Baud rate	38,4 kbaud (COM2)
Cycle time	≥ 2.3 ms
Process data length	24 bit
SIO-mode	No
Process data (cyclic)	Process pressure
Diagnostic data (acyclic)	Process temperature

### Housing

Style	Compact transmitter
Overall size	Refer to section "Dimensional drawings"
Material	AISI 316L (1.4404)

### Electrical connection

Connector	DIN EN 175301-803 A (DIN 43650 A), 4-pin M12-A, 4-pin M12-A, 5-pin, stainless steel, IO-Link output
Cable gland	Cable Ø 8 ... 10, stainless steel
Cable outlet	1.5 m, 3-wire, shielded

### Power supply

Voltage supply range	13 ... 30 V DC , with voltage output 8 ... 30 V DC , with current output 18 30 V DC , with IO-Link
----------------------	--

### ATEX II 1/2G Ex ia IIC T4/T6 Ga/Gb

Please note	For the application in Ex zone you have to respect the conditions mentioned in the ATEX Type Examination Certificate (SEV 11 ATEX 0129). You will find the relevant certificates and instructions at <a href="http://www.baumer.com">www.baumer.com</a>
Maximum values for barrier selection, Ui	30 V DC , max.
Maximum values for barrier selection, li	100 mA

### ATEX II 1/2G Ex ia IIC T4/T6 Ga/Gb

Maximum values for barrier selection, Pi	750 mW
Internal capacitance, Ci	31 nF
Internal inductance, Li	3 µH

### ATEX II 1D Ex ia IIIC T (200) 107°C IP6X Da

Please note	For the application in Ex zone you have to respect the conditions mentioned in the ATEX Type Examination Certificate (SEV 11 ATEX 0129). You will find the relevant certificates and instructions at <a href="http://www.baumer.com">www.baumer.com</a>
Voltage supply range, Un	30 V DC , max.
Degree of protection for cable accessories	IP 65

### ATEX II 1G Ex ia IIC T4/T6 Ga

Please note	For the application in Ex zone you have to respect the conditions mentioned in the ATEX Type Examination Certificate (SEV 11 ATEX 0129). You will find the relevant certificates and instructions at <a href="http://www.baumer.com">www.baumer.com</a>
Maximum values for barrier selection, Ui	30 V DC , max.
Maximum values for barrier selection, li	100 mA
Maximum values for barrier selection, Pi	750 mW
Internal capacitance, Ci	31 nF
Internal inductance, Li	3 µH

Maximum values for barrier selection, Ui	30 V DC , max.
--	----------------

Maximum values for barrier selection, li	100 mA
--	--------

Maximum values for barrier selection, Pi	750 mW
--	--------

Internal capacitance, Ci	31 nF
--------------------------	-------

Internal inductance, Li	3 µH
-------------------------	------

### Compliance and approvals

EMC	EN 61000-6-2 EN 61000-6-3 EN 61326-2-3
Explosion protection	ATEX II 1/2G Ex ia IIC T4/T6 Ga/Gb ATEX II 1D Ex ia IIIC T107 °C IP6X Da ATEX II 1G Ex ia IIC T4/T6 Ga

## Operating conditions

Measuring range (bar)								Proof pressure (bar)	Burst Pressure (bar)
0 ... 0,1    0 ... 0,16    0 ... 0,25								1	2
-0,1 ... 0,1	-0,2 ... 0,2	-1 ... 0	-1 ... 0,6	0 ... 0,4	0 ... 0,6	0 ... 1	3	6	
	-1 ... 1,5	-1 ... 3	-1 ... 5	0 ... 1,6	0 ... 2	0 ... 2,5	15	30	
		-1 ... 9	-1 ... 15	0 ... 6	0 ... 10	0 ... 16	60	120	
			-1 ... 24	0 ... 25			70	140	
			-1 ... 39	0 ... 40			135	270	


# PBMN low pressure

Fully welded pressure transmitter for industrial applications


PBMN-2#####2##0##

## Dimensional drawings (mm)


### Housing




Housing with connector M12-A, 4-pin



Housing with connector DIN EN 175301-803 A (DIN 43650 A), 4-pin




Housing with cable outlet, 3-wire, 1.5 m length




Field housing with cable gland


### Process connection



G30-02  
G 1/4 B EN 837-1 (BCID: G30)



G31-03  
G 1/2 B EN 837-1 (BCID: G31)



N01-04  
1/4-18 NPT (BCID: N01)


# PBMN low pressure

Fully welded pressure transmitter for industrial applications


PBMN-2#####2##0##

## Dimensional drawings (mm)


### Process connection




N02-05  
1/2-14 NPT (BCID: N02)




G50-06  
G 1/4 A DIN 3852-E (BCID: G50)



G51-09  
G 1/2 A DIN 3852-E (BCID: G51)



G51-19  
G 1/2 A DIN 3852-E, hole Ø 10 mm (BCID: G51)



G21-12  
G 1/4 A ISO 228-1 female thread (BCID: G21)

# PBMN low pressure

Fully welded pressure transmitter for industrial applications

PBMN-2#####2##0##

## Electrical connection

Output signal	Equivalent circuit	Electrical connection	Function	Pin assignment
4 ... 20 mA (2-wire)			+Vs	1
			Iout	3
			Frame Ground	Plug thread
			n.c.	2, 4
0 ... 10 V (3-wire)			+Vs	1
			Uout	2, 4
			GND (0 V)	3
			Frame Ground	Plug thread
			n.c.	3, 4
IO-Link (3-wire)			+Vs	1
			GND (0 V)	3
			SW1, IO-Link	4
			Iout	2
			Frame Ground	Plug thread
			n.c.	5

## Ordering information

Ordering key - Configuration possibilities see website

# PBMN low pressure

Fully welded pressure transmitter for industrial applications

PBMN-2#####2##0##

## Ordering information

Ordering key - Configuration possibilities see website

	PBMN	-	2	#	###	#	##	##	##	2	#	#	0	#	#
<b>Product</b>	PBMN														
<b>Housing material</b>															
Stainless steel 1.4404 AISI 316L										2					
<b>Accuracy</b>															
±0.25 % FS															4
±0.10 % FS															5
<b>Measuring range</b>															
0...0,1 bar (EN)															B08
0...0,16 bar (EN)															B09
0 ... 0.25 bar (EN)															B10
0 ... 0.4 bar (EN)															B11
0...0,6 bar (EN)															B12
0...1 bar (EN)															B15
0...1,6 bar (EN)															B16
0...2 bar (EN)															B17
0 ... 2.5 bar (EN)															B18
0 ... 4 bar (EN)															B19
0...12 bar (EN)															B1K
-1...39 bar (EN)															B1L
0 ... 6 bar (EN)															B20
0 ... 10 bar (EN)															B22
0 ... 16 bar (EN)															B24
0...20 bar (EN)															B25
0...25 bar (EN)															B26
0 ... 40 bar (EN)															B27
-0,1...0,1 bar (EN)															B2H
-0,2...0,2 bar (EN)															B4G
-0,6...0 bar (EN)															B58
-1...0 bar (EN)															B59
-1...0,6 bar (EN)															B72
-1...1 bar (EN)															B73
-1 ... 1,5 bar (EN)															B74
-1...2 bar (EN)															B75
-1...3 bar (EN)															B76
-1...5 bar (EN)															B77
-1...9 bar (EN)															B79
-1...15 bar (EN)															B81
-1...24 bar (EN)															B82
0...5 bar (EN)															B98
<b>Kind of pressure</b>															
Relative (gauged)															R
Absolute															A

# PBMN low pressure

Fully welded pressure transmitter for industrial applications

PBMN-2#####2##0##

## Ordering information

Ordering key - Configuration possibilities see website

	PBMN	-	2	#	###	#	##	##	##	2	#	#	0	#	#
<b>Output signal</b>															
20...4 mA															A0
4...20 mA															A1
0...10 V															A2
1...5 V															A3
0...5 V															A4
0.5...4.5 V															A5
10...0 V															A7
IO-Link or 4...20 mA V1															M1
<b>Output Connection</b>															
M12-A, 4-pin															14
M12-A, 5-pin															15
DIN EN 175301-803 A (DIN 43650 A), 4-pin															44
Cable outlet 1.5 m, 3-wire, shielded															53
Connection head, cable gland IP67															54
<b>Process connection</b>															
G 1/4 B EN 837-1 (G30)															02
G 1/2 B EN 837-1 (G31)															03
1/4-18 NPT (N01)															04
1/2-14 NPT (N02)															05
G 1/4 A DIN 3852-E (G50)															06
M20 × 1.5 ISO 261 / ISO 965 (M08)															07
G 1/2 A DIN 3852-E (G51)															09
G 1/4 A ISO 228-1 female thread (G21)															12
G 1/2 A DIN 3852-E, hole Ø 10 mm (G52)															19
G 1/4 B EN 837-1 with integrated damping element (P ≤ 600 bar) (G30)															22
G 1/2 B EN 837-1 with integrated damping element (P ≤ 600 bar) (G31)															23
1/4-18 NPT with integrated damping element (P ≤ 1000 bar) (N01)															24
1/2-14 NPT with integrated damping element (P ≤ 1000 bar) (N02)															25
G 1/4 A DIN 3852-E, pressure channel 0.6 mm (G50)															26
G 1/2 A DIN 3852-E with integrated damping element (P ≤ 600 bar) (G51)															29
<b>Process connection material</b>															
Stainless steel 1.4404 AISI 316L															2
<b>Seal</b>															
None															0
NBR standard															1
FKM (Viton®)															3
<b>Oil filling</b>															
Standard oil															1
NSF H1 listed (FDA approved)															2
<b>Display</b>															
Without display															0
<b>ATEX</b>															
Standard safety															0
ATEX according to SEV 11 ATEX 0129															1

# PBMN low pressure

Fully welded pressure transmitter for industrial applications

PBMN-2#####2#0##

## Ordering information

Ordering key - Configuration possibilities see website

PBMN - 2 # ### # ## ## ## 2 # # 0 # #

### Approvals

Standard approvals	0
EAC	7