

PT20H

Hygienic compact RTD temperature sensor

PT20H-####.1###2##.2#000##.####

Overview

- Precision measurement from -50 ... 250 °C
- Integrated 4 ... 20 mA transmitter with high accuracy
- Fast power-up time < 2 s
- All parts welded together
- Customer-specific immersion depth down to 3000 mm
- IO-Link Dual Channel for easy commissioning



Picture similar



Technical data

Performance characteristics

Pt100 accuracy class (EN 60751)	1/1 B ± (0.3 + 0.005 × t)°C 1/1 A ± (0.15 + 0.002 × t)°C 1/3 B ± 1/3 × (0.3 + 0.005 × t)°C 1/6 B ± 1/6 × (0.3 + 0.005 × t)°C
Max. output error	≤ 0.06 % FSR @ 25 °C Including input accuracy, output accuracy and repeatability
Thermal response time, T90	RTD element and transmitter combined < 3.0 s , Ø3 mm < 6.1 s , Ø6 mm
Temperature drift (by ambient)	< 0.025 K/K + 0.01 % FSR/K
Process temperature	Refer to section "Operating conditions"

Process connection

Connection variants	Refer to section "Dimensional drawings"
Sensor length	≤ 3000 mm
Sensor diameter outside	ø 6 mm
Mounting position	Any, top, bottom, side
Standard response tip	ø 6 mm
Fast response tip	ø 3 mm
Sensor tube material	AISI 316L (1.4404)
Surface roughness wetted parts	Ra ≤ 0.8 µm

Ambient conditions

Operating temperature range	-40 ... 85 °C
Storage temperature range	-50 ... 85 °C

Ambient conditions

Degree of protection (EN 60529)	Connector DIN EN 175301-803 A (DIN 43650 A), 4-pin: IP65 Connector M12-A, 4-pin: IP68 , with appropriate cable (336 h @ 10 mH2O) IP69K , with appropriate cable
Humidity	≤ 100 % RH , condensing
Vibration (sinusoidal) (EN 60068-2-6)	1.6 mm p-p (2 ... 25 Hz), 4 g (25 ... 100 Hz), 1 octave / min. GL, test 2

IO-Link interface

IO-Link version	1.1
Device profile	Smart Sensor Profile
IO-Link port type	Class A
Baud rate	38,4 kbaud (COM2)
Process data length	72 bit
SIO-mode	Yes
Process data (cyclic)	Switch state State of alert Process temperature Unit temperature Signal analog output 1
Dual Channel	IO-Link / Analogue

Housing

Style	Compact transmitter
Overall size	Refer to section "Dimensional drawings"
Material	AISI 304 (1.4301)

Electrical connection

Connector	DIN EN 175301-803 A (DIN 43650 A), 4-pin M12-A, 4-pin
-----------	--

PT20H

Hygienic compact RTD temperature sensor

PT20H-####.1###2##.2#000##.####

Technical data

Power supply

Voltage supply range	7 ... 35 V DC (Standard version)
	10 ... 35 V DC (Dual Channel version)
	18 ... 30 V DC (Dual Channel version, IO-Link communication)

Power-up time	< 2 s
---------------	-------

Reverse polarity protection	Yes
-----------------------------	-----

Factory settings

Output range	0 ... 150 °C
--------------	--------------

Factory settings

Damping	0 s
---------	-----

Output at sensor fault	23 mA
------------------------	-------

Compliance and approvals

EMC	EN 61326-1
-----	------------

Hygiene	3-A (74-07) EHEDG EL Class I
---------	---------------------------------

Safety	cULus listed, E527512
--------	-----------------------

Transmitter

Input

Min. measuring span	10 °C
---------------------	-------

Sample time	< 0.1 s
-------------	---------

Accuracy	± 0.05 °C (-50 ... 200 °C)
	± 0.06 °C (200 ... 250 °C)

Error detection delay	< 2 s
-----------------------	-------

Output

Output type	PNP
	NPN
	Digital (push-pull)
	4 ... 20 mA, 2-wire
20 ... 4 mA, 2-wire	

Switching logic	Active high
	Active low

Voltage drop	PNP: (+Vs - 1,2 V) ± 0.5 V, Rload ≥ 10 kΩ
	NPN: (-Vs + 1,5 V) ± 0.5 V, Rload ≥ 10 kΩ

Resolution	14 bit
------------	--------

Ripple immunity	< 1 % FSR (1 Vrms, 50Hz...1kHz)
-----------------	---------------------------------

Shunt resistance	Rs ≤ (V DC - 7 V)/0.023 A (Standard version)
	Rs ≤ (V DC - 10 V)/0.023 A (Dual Channel version)

Current rating	100 mA, max.
----------------	--------------

Off leak current	< 100 µA
------------------	----------

Short circuit protection	Yes
--------------------------	-----

Damping	0.0 ... 60.0 s, programmable
---------	------------------------------

Up/Down scaling limits	23 mA / 3.5 mA
------------------------	----------------

Operating conditions

Ordering key	Process connection	BCID	Process pressure (bar)	Continuous		
				Process temperature Standard @ Tamb ≤ 20 °C (° C)	Process temperature With cooling neck, Sensor tip Ø3 mm @ Tamb ≤ 20 °C (° C)	Process temperature With cooling neck, Sensor tip Ø6 mm @ Tamb ≤ 20 °C (° C)
A020	M12 x 1.5 hygienic	A02	-1 ... 40	-50 ... 125	-50 ... 200	-50 ... 250
A030	G 1/2 A hygienic	A03	-1 ... 40	-50 ... 125	-50 ... 200	-50 ... 250
B010	BHC 3A DN 38	B01	-1 ... 40	-50 ... 125	-50 ... 200	-50 ... 250
C040	ISO 2852 (Tri-Clamp), DN 33.7;38 Ø 50.5	C04	-1 ... 40	-50 ... 125	-50 ... 200	-50 ... 250
C010	Tri-Clamp, DN3/4", Ø25.0	C01	-1 ... 40	-50 ... 125	-50 ... 200	-50 ... 250

For further information on permissible process and ambient temperatures, please refer to the operating instructions.


PT20H

Hygienic compact RTD temperature sensor


PT20H-####.1###2##.2#000##.####

Dimensional drawings (mm)


Housing




Housing with Dual Channel transmitter and King Crown connector M12-A, 4-pin (with LED)




Housing with Dual Channel transmitter and connector M12-A, 4-pin



Housing with transmitter and connector M12-A, 4-pin




Housing with transmitter and connector DIN EN 175301-803 A (DIN 43650 A), 4-pin




Cooling neck


Process connection



M12 × 1.5 hygienic (BCID: A02)



G 1/2 A hygienic (BCID: A03)



BHC 3A DN 38 (BCID: B01)
3-A / EHEDG certified


PT20H

Hygienic compact RTD temperature sensor


PT20H-####.1###2##.2#000##.####

Dimensional drawings (mm)

Process connection




Tri-Clamp Ø 50.5 (BCID: C04),
3-A / EHEDG certified



Tri-Clamp Ø 25 (BCID: C01)
3-A



Standard response tip



Fast response tip

Electrical connection

Output type	Electrical connection	Equivalent circuit	Function	Pin assignment							
	M12-A, 4-pin, stainless steel										
Standard version 4 ... 20 mA, 2-wire			<table border="1"> <tr><td>+Vs</td><td>1</td></tr> <tr><td>lout</td><td>2, 3</td></tr> <tr><td>N.C.</td><td>4</td></tr> <tr><td>Frame ground</td><td>Plug thread</td></tr> </table>	+Vs	1	lout	2, 3	N.C.	4	Frame ground	Plug thread
+Vs	1										
lout	2, 3										
N.C.	4										
Frame ground	Plug thread										
	DIN EN 175301-803 A (DIN 43650 A), 4-pin										
Standard version 4 ... 20 mA, 2-wire			<table border="1"> <tr><td>+Vs</td><td>1</td></tr> <tr><td>lout</td><td>2</td></tr> <tr><td>N.C.</td><td>3</td></tr> <tr><td>Frame ground</td><td>Grounding lug</td></tr> </table>	+Vs	1	lout	2	N.C.	3	Frame ground	Grounding lug
+Vs	1										
lout	2										
N.C.	3										
Frame ground	Grounding lug										

PT20H

Hygienic compact RTD temperature sensor

PT20H-####.1###2##.2#000##.####

Electrical connection

Output type	Electrical connection	Equivalent circuit	Function	Pin assignment
	M12-A, 4-pin, stainless steel			
Dual Channel version 4 ... 20 mA, 2-wire			+Vs lout N.C. Frame ground	1 2 3, 4 Plug thread
Dual Channel version IO-Link + 4 ... 20 mA PNP			+Vs SW1 (IO-Link) lout GND (0 V) Frame ground	1 4 2 3 Plug thread
Dual Channel version IO-Link + 4 ... 20 mA NPN			+Vs SW1 (IO-Link) lout GND (0 V) Frame ground	1 4 2 3 Plug thread
Dual Channel version IO-Link + 4 ... 20 mA Digital (push-pull)			+Vs SW1 (IO-Link) lout GND (0 V) Frame ground	1 4 2 3 Plug thread

PT20H

Hygienic compact RTD temperature sensor

PT20H-####.1###2##.2#000##.####

Ordering information

Ordering key - Configuration possibilities see website

Product	PT20H	-	####	.	#	#	#	#	2	#	#	.	2	#	0	0	0	#	#	.	####
Product	PT20H																				
Process connection																					
M12 x 1.5 hygienic (A02)																					A020
G 1/2 A hygienic (A03)																					A030
BHC 3A DN38 (B01)																					B010
DIN 32676-C (Tri-Clamp), DN 3/4, Ø 25.0 (C01)																					C010
ISO 2852 (Tri-Clamp) DN38 (C04)																					C040
Sensor tip																					
Standard tip (Ø6 mm)																					1
Fast response tip (Ø3 mm)																					3
Sensor element																					
Pt100 1/1 B EN 60751, single, 2-wire																					1
Pt100 1/3 B EN 60751, single, 2-wire																					3
Pt100 1/6 B EN 60751, single, 2-wire																					5
Pt100 1/1 A EN 60751, single, 2-wire																					7
Pt100 1/1 B EN 60751, single, 4-wire																					A
Pt100 1/3 B EN 60751, single, 4-wire																					B
Pt100 1/6 B EN 60751, single, 4-wire																					C
Pt100 1/1 A EN 60751, single, 4-wire																					D
Cooling neck																					
Without cooling neck																					0
With cooling neck																					4
Process temperature																					
-50...125°C																					1
-50...250°C																					3
Max. process pressure																					
40 bar																					2
Interface																					
4...20 mA																					1
IO-Link Dual Channel, 4...20 mA																					2
Electrical connection																					
M12-A, 4 pin, stainless steel, with integrated transmitter																					2
M12-A, 4 pin, stainless steel KingCrown, with integrated transmitter (with LED)																					3
DIN EN 175301-803 A (DIN 43650 A), 4-pin, with integrated transmitter																					5
Wetted parts material																					
AISI 316L (1.4404)																					2
Surface roughness																					
Ra ≤ 0.8 µm																					1
Ra ≤ 0.4 µm																					2
Electropolished, Ra ≤ 0,8 µm																					3
Electropolished, Ra ≤ 0,4 µm																					4
Gasket material																					
Without																					0
Explosion protection																					
Without																					0
Industrial approvals																					
Standard																					0

PT20H

Hygienic compact RTD temperature sensor

PT20H-####.1###2##.2#000##.####

Ordering information

Ordering key - Configuration possibilities see website

	PT20H	-	####	.	#	#	#	#	2	#	#	.	2	#	0	0	0	#	#	.	####
Special approvals																					
	Standard																				0
	3-A																				1
	3-A / EHEDG																				3
Configuration																					
	Factory settings																				0
	Customer-specific																				1
Sensor tube length (mm)																					
	20 - 3000																				####

(1) Including female power connector