

V CXG.2-241M.XC

Gigabit Ethernet, 24.4 Megapixel, Monochrome

Article number: 11708137

Overview

- 5312 x 4600 px
- Sony IMX540
- 1.2" CMOS
- 5 fps
- Gigabit Ethernet
- Cooling pipe integrated in the housing (optional use)



Picture similar



GEN<i>i>CAM



Technical data

Sensor information

Sensor	Sony IMX540 Gen4
Mono/Color	Mono
Sensor type	1.2" CMOS
Shutter type	Global shutter
Resolution	5312 × 4600 px
Pixel size	2.74 × 2.74 μm
Exposure time	0.039 ... 60000 ms

Data quality (EMVA 1288 typical)

Dark noise	2.29 e-
Saturation capacity	9531 e-
Dynamic range	70.2 dB
Signal-to-noise ratio	39.8 dB
Quantum efficiency	70.6 % @ 536 nm

Acquisition formats

Image formats, interface frame rate max.	Full Frame, 5312 × 4600 px, max. 5 fps Binning 2×2, 2656 × 2296 px, max. 19 fps Binning 2×1, 2656 × 4600 px, max. 5 fps Binning 1×2, 5312 × 2300 px, max. 5 fps
Image formats, acquisition frame rate max. (Burst Mode)	Full Frame, 5312 × 4600 px, max. 5 fps
Pixel formats	Mono8 Mono10 Mono12 Mono12 Packed

Image preprocessing

Analog controls	Gain (0 ... 48 dB) Offset (0 ... 255 LSB 12 Bit)
Color models	Mono

Camera features

Basic Functions	Exposure Gain Trigger / Exposure Active (Flash) Binning 2x2 Partial Scan Offset Free Running Mode (Live Image)
Auto Functions	Exposure Auto Gain Auto
Image Pre-processing	Image Flipping (X/Y) LUT / Gamma
Acquisition / Interface	Burst Mode Adjustable Framerate Device Link Throughput Limit Internal Image Buffer
Synchronization	free running trigger
Trigger sources	Hardware Software ActionCommand
Trigger delay	0 ... 2 s, tracking and buffering of up to 256 trigger signals
Process Synchronization	Events Timer Trigger Delay Debouncer Counter Sequencer Trigger via Action CMD (GigE) Additional Output Modes (e.g. Trigger Ready) Chunk data inside transferred image Encoder support via Counter End trigger source

2024-12-02 The product features and technical data specified do not express or imply any warranty. Technical modifications subject to change.

VCXG.2-241M.XC

Gigabit Ethernet, 24.4 Megapixel, Monochrome

Article number: 11708137

Technical data

Camera features

Additional Functions	User Set Integrated temperature sensor Readable additional information (e.g. sensor information)
Calibration data	Camera calibration data (user defined storage for intrinsic / extrinsic camera parameters, and geometry distortion values) Customer data storage (128 bytes user defined)
Internal image buffer	140 MB 2 image (Trigger Mode) 1 image (Free Running Mode)

Interfaces and connectors

Data interface	Gigabit Ethernet, Transfer rate 1000 Mbit/s, Connector: 8P8C Modular Jack (RJ45), screwable type
----------------	--

Mechanical data

Lens mount	C-mount
Width	36 mm
Height	36 mm
Depth	46.1 mm
Weight	≤ 110 g
Material	zinc die casting, baked varnish

Electrical data

Voltage supply range +Vs	12 ... 24 V DC (external power supply) 36 ... 57 V DC (Power over Ethernet)
--------------------------	--

Electrical data

Power consumption	Approx. 3.4 W @ 12 VDC and 5 fps Approx. 4.1 W @ 48 VDC (PoE) and 5 fps
-------------------	--

Non-volatile memory

Flash memory size	128 kB
-------------------	--------

Environmental conditions

Operating temperature	0 ... +65 ° @ T = measurement point
Storage temperature	-20 ... +70 °C
Humidity	10 ... 90 % (non-condensing)
Protection class	IP 40 (with mounted lens and cable)

Digital I/Os


Lines	1 input line 1 output line 2 general purpose lines
-------	--

Output line sources	Off Exposure Active Timer1 Readout Active User0 User1 User2 TriggerReady
---------------------	---

Conformity

Conformity	CE UL recognized RoHS
------------	-----------------------------

Dimension drawing



Principle

