

VCXG.2-51MP

Gigabit Ethernet, 5 Megapixel, mono polarized

Article number: 11707067

Overview

- 2448 x 2048 px
- Sony IMX264 Gen2
- 2/3" CMOS
- 35 fps
- Gigabit Ethernet



Picture similar



GEN<i>i>CAM



Technical data

Sensor information

Sensor	Sony IMX264 Gen2
Mono/Color	Mono polarized
Sensor type	2/3" CMOS
Shutter type	Global shutter
Resolution	2464 × 2048 px
Pixel size	3.45 × 3.45 μm
Exposure time	0.001 ... 60000 ms

Data quality (EMVA 1288 typical)

Dark noise	2.02 e-
Saturation capacity	9122 e-
Dynamic range	70.6 dB
Signal-to-noise ratio	39.6 dB
Quantum efficiency	24.4 % @ 533 nm

Acquisition formats

Image formats, interface frame rate max.	Full Frame, 2448 × 2048 px, max. 24 fps Binning 2×2, 1224 × 1024 px, max. 35 fps Binning 2×1, 1224 × 2048 px, max. 35 fps Binning 1×2, 2448 × 1024 px, max. 35 fps
Image formats, acquisition frame rate max. (Burst Mode)	Full Frame, 2448 × 2048 px, max. 35 fps
Pixel formats	Mono8 Mono10 Mono12 Mono12 Packed

Image preprocessing

Analog controls	Gain (0 ... 48 dB) Offset (0 ... 255 LSB 12 Bit)
Color models	Mono Mono polarized

Camera features

Basic Functions	Exposure Gain / Color Gain Trigger / Exposure Active (Flash) Binning 2x2 Partial Scan Offset Free Running Mode (Live Image)
Auto Functions	Exposure Auto Gain Auto
Image Pre-processing	Image Flipping (X/Y) LUT / Gamma
Acquisition / Interface	Burst Mode Adjustable Framerate Short Exposure Time Enable Device Link Throughput Limit Internal Image Buffer
Synchronization	free running trigger
Trigger sources	Hardware Software ActionCommand
Trigger delay	0 ... 2 s, tracking and buffering of up to 256 trigger signals

The product features and technical data specified do not express or imply any warranty. Technical modifications subject to change. 2025-01-23

VCXG.2-51MP

Gigabit Ethernet, 5 Megapixel, mono polarized

Article number: 11707067

Technical data

Camera features

Process Synchronization	<ul style="list-style-type: none"> Events Timer Trigger Delay Debouncer Counter Sequencer Trigger via Action CMD (GigE) Additional Output Modes (e.g. Trigger Ready) Chunk data inside transferred image Encoder support via Counter End trigger source
-------------------------	---

Additional Functions	<ul style="list-style-type: none"> User Set Integrated temperature sensor Readable additional information (e.g. sensor information)
----------------------	--

Calibration data	<ul style="list-style-type: none"> Camera calibration data (user defined storage for intrinsic / extrinsic camera parameters, and geometry distortion values) Customer data storage (128 bytes user defined)
------------------	--

Internal image buffer	<ul style="list-style-type: none"> 115 MB 8 images (Trigger Mode) 1 image (Free Running Mode)
-----------------------	--

Interfaces and connectors

Data interface	Gigabit Ethernet, Transfer rate 1000 Mbits/sec, Fast Ethernet, Transfer Rate 100 Mbits/sec, Connector: 8P8C Modular Jack (RJ45), screwable TYPE090 (according to GigE Vision Mechanical Supplement)
----------------	---

Process interface	M8 / 8 pins (SACC-DSI-M8MS-8CON-M8-L180)
-------------------	--

Interfaces and connectors

Power supply	via M8/8 pins or Power over Ethernet (PoE)
--------------	--

Mechanical data

Lens mount	C-mount
Width	29 mm
Height	29 mm
Depth	49 mm
Weight	≤ 120 g
Material	zinc die casting, baked varnish

Electrical data

Power consumption	<ul style="list-style-type: none"> Approx. 2.8 W @ 12 VDC and 24 fps Approx. 3.5 W @ 48 VDC (PoE) and 24 fps
Operating voltage	0

Non-volatile memory

Flash memory size	128 kB
-------------------	--------

Environmental conditions

Operating temperature	0 ... +65 ° @ T = measurement point
Storage temperature	-20 ... +70 °C
Humidity	10 ... 90 % (non-condensing)
Protection class	IP 40 (with mounted lens and cable)

Digital I/Os

Lines	<ul style="list-style-type: none"> 1 input line 1 output line 2 general purpose lines
-------	--

Conformity

Conformity	<ul style="list-style-type: none"> CE RoHS UL recognized
------------	---

VCXG.2-51MP

Gigabit Ethernet, 5 Megapixel, mono polarized

Article number: 11707067

Dimension drawing

