

## V CXU.2-57C

USB 3.0, 5 Megapixel, Color

Article number: 11708187

### Overview

- 2464 × 2048 px
- Sony IMX548
- 1/1.8" CMOS
- 75 fps
- USB 3.0



Picture similar



GEN<i>i>CAM



### Technical data

#### Sensor information

Sensor	Sony IMX548 Gen4
Mono/Color	Color
Sensor type	1/1.8" CMOS
Shutter type	Global shutter
Resolution	2464 × 2048 px
Pixel size	2.74 × 2.74 μm
Exposure time	0.001 ... 60000 ms

#### Acquisition formats

Image formats, interface frame rate max.	Full Frame, 2464 × 2048 px, max. 75 fps Binning 2×2, 1232 × 1024 px, max. 75 fps Binning 2×1, 1232 × 2048 px, max. 75 fps Binning 1×2, 2464 × 1024 px, max. 75 fps
--	---

Image formats, acquisition frame rate max. (Burst Mode)	Full Frame, 2464 × 2048 px, max. 75 fps
---	---

Pixel formats	BayerRG8 BayerRG10 BayerRG12 BayerRG12 Packed Mono8 Mono10 Mono12 Mono12 Packed RGB8 BGR8
---------------	--

#### Image preprocessing

Analog controls	Gain (0 ... 48 dB) Offset (0 ... 255 LSB 12 Bit)
-----------------	---

#### Image preprocessing

Color models	Mono Raw Bayer RGB BGR
Color processing	Integrated color processor for high quality color calculation

#### Camera features

Basic Functions	Exposure Gain / Color Gain Trigger / Exposure Active (Flash) Binning 2x2 Partial Scan Offset Free Running Mode (Live Image)
Auto Functions	Exposure Auto Gain Auto White Balance Auto Color Transformation Auto
Image Pre-processing	Image Flipping (X/Y) Color Processing (RGB, BGR, Mono) Color Enhancement (with optimized ColorTransformationMatrix) LUT / Gamma
Acquisition / Interface	Burst Mode Adjustable Framerate Device Link Throughput Limit Internal Image Buffer
Synchronization	free running trigger

2023-07-18 The product features and technical data specified do not express or imply any warranty. Technical modifications subject to change.

# VCXU.2-57C

USB 3.0, 5 Megapixel, Color

Article number: 11708187

## Technical data

### Camera features

Trigger sources	Hardware Software ActionCommand
Trigger delay	0 ... 2 sec, tracking and buffering of up to 256 trigger signals
Process Synchronization	Events Timer Trigger Delay Debouncer Counter Chunk data inside transferred image Encoder support via Counter End trigger source
Additional Functions	User Set Integrated temperature sensor Readable additional information (e.g. sensor information)
Calibration data	Integrated color correction matrix (3000 K, 5000 K, 6500 K, 9500 K, and user defined) Camera calibration data (user defined storage for intrinsic / extrinsic camera parameters, and geometry distortion values) Customer data storage (128 bytes user defined)
Internal image buffer	141 MB 4 image (Trigger Mode) 1 image (Free Running Mode)

### Interfaces and connectors

Data interface	USB 3.0, Transfer Rate 5000 Mbits/sec, Connector: USB 3.0 Micro B
Process interface	M8 / 8 pins (SACC-DSI-M8MS-8CON-M8-L180)
Power supply	via USB 3.0 interface

### Mechanical data

Lens mount	C-mount
Width	29 mm
Height	29 mm
Depth	38 mm
Weight	≤ 90 g
Material	zinc die casting, baked varnish

### Electrical data

Power consumption	Approx. 2.7 W @ 75 fps
Operating voltage	5 VDC (via USB3.0 interface)

### Non-volatile memory

Flash memory size	128 kB
-------------------	--------

### Environmental conditions

Operating temperature	0 ... +65 ° @ T = measurement point
Humidity	10 ... 90 % (non-condensing)
Protection class	IP 40

### Digital I/Os

Lines	1 input line 1 output line 2 general purpose lines
Output line sources	Off Exposure Active Timer1 Readout Active User0 User1 User2 TriggerReady

### Conformity

Conformity	CE RoHS
------------	------------

# VCXU.2-57C

USB 3.0, 5 Megapixel, Color

Article number: 11708187

## Dimension drawing

