

## VCXU.2-13M

USB 3.0, 1,3 Megapixel, Monochrome

Article number: 11708175

### Overview

- 1280 x 1024 px
- onsemi PYTHON1300
- 1/2" CMOS
- 222 fps
- USB 3.0



Picture similar



GEN<i>i>CAM



### Technical data

#### Sensor information

Sensor	onsemi PYTHON1300
Mono/Color	Mono
Sensor type	1/2" CMOS
Shutter type	Global shutter
Resolution	1280 × 1024 px
Pixel size	4.8 × 4.8 μm
Exposure time	0.02 ... 1000 ms

#### Data quality (EMVA 1288 typical)

Dark noise	9.78 e-
Saturation capacity	6952 e-
Dynamic range	56.3 dB
Signal-to-noise ratio	38.4 dB
Quantum efficiency	53.5 % @ 536 nm

#### Acquisition formats

Image formats, interface frame rate max.	Full Frame, 1280 × 1024 px, max. 222 fps Binning 2×2, 640 × 512 px, max. 222 fps Binning 2×1, 640 × 1024 px, max. 222 fps Binning 1×2, 1280 × 512 px, max. 222 fps
Image formats, acquisition frame rate max. (Burst Mode)	Full Frame, 1280 × 1024 px, max. 222 fps
Pixel formats	Mono8 Mono10

#### Image preprocessing

Analog controls	Gain (0 ... 48 dB) Offset (0 ... 255 LSB 12 Bit)
-----------------	---

#### Image preprocessing

Color models	Mono
--------------	------

#### Camera features

Basic Functions	Exposure Gain Trigger / Exposure Active (Flash) Binning 2x2 Partial Scan Offset Free Running Mode (Live Image)
Auto Functions	Exposure Auto Gain Auto
Image Pre-processing	Image Flipping (X/Y) LUT / Gamma
Acquisition / Interface	Burst Mode Adjustable Framerate Device Link Throughput Limit Internal Image Buffer
Synchronization	free running trigger
Trigger sources	Hardware Software
Trigger delay	0 ... 2 s, tracking and buffering of up to 256 trigger signals

# VCXU.2-13M

USB 3.0, 1,3 Megapixel, Monochrome

Article number: 11708175

## Technical data

### Camera features

Process Synchronization	Events Timer Trigger Delay Debouncer Counter Sequencer Trigger via Action CMD (GigE) Additional Output Modes (e.g. Trigger Ready) Chunk data inside transferred image Encoder support via Counter End trigger source
-------------------------	---

Additional Functions	User Set Integrated temperature sensor Readable additional information (e.g. sensor information)
----------------------	--

Calibration data	Camera calibration data (user defined storage for intrinsic / extrinsic camera parameters, and geometry distortion values) Customer data storage (128 bytes user defined)
------------------	--

Internal image buffer	477 MB 127 images (Trigger Mode) 1 image (Free Running Mode)
-----------------------	--

### Interfaces and connectors

Data interface	USB 3.0, Transfer Rate 5000 Mbits/sec, Connector: USB 3.0 Micro B
Process interface	M8 / 8 pins (SACC-DSI-M8MS-8CON-M8-L180)

### Interfaces and connectors

Power supply	via USB 3.0 interface
--------------	-----------------------

### Mechanical data

Lens mount	C-mount
Width	29 mm
Height	29 mm
Depth	38 mm
Weight	≤ 90 g
Material	zinc die casting, baked varnish

### Electrical data

Power consumption	Approx. 2.7 W @ 222 fps
Operating voltage	5 VDC (via USB3.0 interface)

### Non-volatile memory

Flash memory size	128 kB
-------------------	--------

### Environmental conditions

Operating temperature	0 ... +65 ° @ T = measurement point
Storage temperature	-20 ... +70 °C
Humidity	10 ... 90 % (non-condensing)
Protection class	IP 40 (with mounted lens and cable)

### Digital I/Os

Lines	1 input line 1 output line 2 general purpose lines
-------	--

### Conformity

Conformity	CE RoHS UL recognized
------------	-----------------------------

## Dimension drawing

