

VCXU.2-65C.R

USB 3.0, 6,2 Megapixel, Color

Article number: 11708177

Overview

- 3072 x 2048 px
- Sony IMX178
- 1/1.8" CMOS
- 47 fps
- USB 3.0



Picture similar



GEN*i*CAM



Technical data

Sensor information

Sensor	Sony IMX178
Mono/Color	Color
Sensor type	1/1.8" CMOS
Shutter type	Rolling shutter Global reset shutter
Resolution	3072 × 2048 px
Pixel size	2.4 × 2.4 μm
Exposure time	0.014 ... 60000 ms

Data quality (EMVA 1288 typical)

Dark noise	2.96 e-
Saturation capacity	14516 e-
Dynamic range	71.9 dB
Signal-to-noise ratio	41.6 dB
Quantum efficiency	56.4 % @ 465 nm 61.7 % @ 536 nm 47.5 % @ 631 nm 59.8 % @ 467 nm 64.7 % @ 533 nm 46.7 % @ 630 nm

Acquisition formats

Image formats, interface frame rate max.	Full Frame, 3072 × 2048 px, max. 47 fps Binning 2×2, 1536 × 1024 px, max. 47 fps Binning 2×1, 1536 × 2048 px, max. 47 fps Binning 1×2, 3072 × 1024 px, max. 47 fps
Image formats, acquisition frame rate max. (Burst Mode)	Full Frame, 3072 × 2048 px, max. 47 fps

Acquisition formats

Pixel formats	BayerRG8 BayerRG10 BayerRG12 BayerRG12 Packed Mono8 Mono10 Mono12 Mono12 Packed RGB8 BGR8
---------------	--

Image preprocessing

Analog controls	Gain (0 ... 26 dB) Offset (0 ... 255 LSB 12 Bit)
Color models	Mono Raw Bayer RGB BGR

Camera features

Basic Functions	Exposure Gain / Color Gain Trigger / Exposure Active (Flash) Binning 2x2 Partial Scan Offset Free Running Mode (Live Image)
Auto Functions	Exposure Auto Gain Auto White Balance Auto Color Transformation Auto

VCXU.2-65C.R

USB 3.0, 6,2 Megapixel, Color

Article number: 11708177

Technical data

Camera features

Image Pre-processing	Image Flipping (X/Y) Color Processing (RGB, BGR, Mono) Color Enhancement (with optimized ColorTransformationMatrix) LUT / Gamma
Acquisition / Interface	Burst Mode Adjustable Framerate Device Link Throughput Limit Internal Image Buffer
Synchronization	free running trigger
Trigger sources	Hardware Software
Trigger delay	0 ... 2 s, tracking and buffering of up to 256 trigger signals
Process Synchronization	Events Timer Trigger Delay Debouncer Counter Trigger via Action CMD (GigE) Additional Output Modes (e.g. Trigger Ready) Chunk data inside transferred image Encoder support via Counter End trigger source
Additional Functions	User Set Integrated temperature sensor Readable additional information (e.g. sensor information)
Calibration data	Integrated color correction matrix (3000 K, 5000 K, 6500 K, 9500 K, and user defined) Camera calibration data (user defined storage for intrinsic / extrinsic camera parameters, and geometry distortion values) Customer data storage (128 bytes user defined)

Camera features

Internal image buffer	450 MB 25 images (Trigger Mode) 1 image (Free Running Mode)
-----------------------	---

Interfaces and connectors

Data interface	USB 3.0, Transfer Rate 5000 Mbits/sec, Connector: USB 3.0 Micro B
Process interface	M8 / 8 pins (SACC-DSI-M8MS-8CON-M8-L180)
Power supply	via USB 3.0 interface

Mechanical data

Lens mount	C-mount
Width	29 mm
Height	29 mm
Depth	38 mm
Weight	≤ 90 g
Material	zinc die casting, baked varnish

Electrical data

Power consumption	Approx. 2.4 W @ 47 fps
Operating voltage	5 VDC (via USB3.0 interface)

Non-volatile memory

Flash memory size	128 kB
-------------------	--------

Environmental conditions

Operating temperature	0 ... +65 ° @ T = measurement point
Storage temperature	-20 ... +70 °C
Humidity	10 ... 90 % (non-condensing)
Protection class	IP 40 (with mounted lens and cable)

Digital I/Os

Lines	1 input line 1 output line 2 general purpose lines
-------	--

Conformity

Conformity	CE RoHS UL recognized
------------	-----------------------------

VCXU.2-65C.R

USB 3.0, 6,2 Megapixel, Color

Article number: 11708177

Dimension drawing

