

Overview

- Computer lens
- 25 mm
- F 1,4-16
- format 2/3"
- M.O.D. 0,3 m
- locating screw for aperture and focus
- C-mount
- suitable for visible and SWIR wavelengths (400 - 1700 nm)



Picture similar

Technical data

General data

Manufacturer Computar

Mechanical data

Lens mount C-mount

Dimensions 33,5 mm × 36 mm

Max. outer diameter 33.5 mm

Max. length (excl. thread) 36 mm

Weight ≤ 71.2 g

Filter thread M 30,5 × 0,5

Lens data

Lens resolution 1.3 MP

Pixel resolution 5 µm

Lens data

Focal length 25 mm

Format 2/3"

Aperture F1.4-16

Aperture control Manual

M.O.D. 0.3 m

Horizontal angle of view 20.0 °

Vertical angle of view 15.1 °

Diagonal angle of view 24.9 °

At image format 8,8 mm × 6,6 mm

Environmental conditions

Operating temperature -10 ... +50 °C