

V CXU.2-57M

USB 3.0, 5 Megapixel, Monochrome

Article number: 11708186

Overview

- 2464 x 2048 px
- Sony IMX548
- 1/1.8" CMOS
- 75 fps
- USB 3.0



Picture similar



GEN*i*CAM



Technical data

Sensor information

Sensor	Sony IMX548 Gen4
Mono/Color	Mono
Sensor type	1/1.8" CMOS
Shutter type	Global shutter
Resolution	2464 × 2048 px
Pixel size	2.74 × 2.74 μm
Exposure time	0.001 ... 60000 ms

Acquisition formats

Image formats, interface frame rate max.	Full Frame, 2464 × 2048 px, max. 75 fps Binning 2×2, 1232 × 1024 px, max. 234 fps Binning 2×1, 1232 × 2048 px, max. 75 fps Binning 1×2, 2464 × 1024 px, max. 75 fps
Image formats, acquisition frame rate max. (Burst Mode)	Full Frame, 2464 × 2048 px, max. 75 fps
Pixel formats	Mono8 Mono10 Mono12 Mono12 Packed

Image preprocessing

Analog controls	Gain (0 ... 48 dB) Offset (0 ... 255 LSB 12 Bit)
Color models	Mono

Camera features

Basic Functions	Exposure Gain Trigger / Exposure Active (Flash) Binning 2x2 Partial Scan Offset Free Running Mode (Live Image)
Auto Functions	Exposure Auto Gain Auto
Image Pre-processing	Image Flipping (X/Y) LUT / Gamma
Acquisition / Interface	Burst Mode Adjustable Framerate Device Link Throughput Limit Internal Image Buffer
Synchronization	free running trigger
Trigger sources	Hardware Software ActionCommand
Trigger delay	0 ... 2 sec, tracking and buffering of up to 256 trigger signals

VCXU.2-57M

USB 3.0, 5 Megapixel, Monochrome

Article number: 11708186

Technical data

Camera features

Process Synchronization	Events Timer Trigger Delay Debouncer Counter Chunk data inside transferred image Encoder support via Counter End trigger source
Additional Functions	User Set Integrated temperature sensor Readable additional information (e.g. sensor information)
Calibration data	Camera calibration data (user defined storage for intrinsic / extrinsic camera parameters, and geometry distortion values) Customer data storage (128 bytes user defined)
Internal image buffer	141 MB 4 image (Trigger Mode) 1 image (Free Running Mode)

Interfaces and connectors

Data interface	USB 3.0, Transfer Rate 5000 Mbits/sec, Connector: USB 3.0 Micro B
Process interface	M8 / 8 pins (SACC-DSI-M8MS-8CON-M8-L180)
Power supply	via USB 3.0 interface

Mechanical data

Lens mount	C-mount
Width	29 mm

Mechanical data

Height	29 mm
Depth	38 mm
Weight	≤ 90 g
Material	zinc die casting, baked varnish

Electrical data

Power consumption	Approx. 2.7 W @ 75 fps
-------------------	------------------------

Non-volatile memory

Flash memory size	128 kB
-------------------	--------

Environmental conditions

Operating temperature	0 ... +65 ° @ T = measurement point
Humidity	10 ... 90 % (non-condensing)
Protection class	IP 40

Digital I/Os

Lines	1 input line 1 output line 2 general purpose lines
-------	--

Output line sources	Off Exposure Active Timer1 Readout Active User0 User1 User2 TriggerReady
---------------------	---

Conformity

Conformity	CE RoHS
------------	------------

Dimension drawing

